

Electro MIR

— Supercontinuum lasers
— SCIENTIFIC
— NIR - MID IR




MID IR SUPERCONTINUUM LASER



ELECTRO MIR

is the new generation of supercontinuum laser delivering a unique spectrum in the Mid-IR. **ELECTRO MIR** is based on LEUKOS' over 10 years' experience in the field of supercontinuum laser.




FEATURES

- Mid IR spectrum up to 4800 nm
- Spatially singlemode
- Total average power up to 800 mW
- Repetition rate > 100 kHz
- Flexible fiber output
- Achromatic collimation
- Maintenance-free
- Long lifetime

APPLICATIONS

- High resolution imaging
- Flow cytometry
- OCT
- Microscopy
- Optical component characterization



LEUKOS
Make a bright future

Electro MIR





MID IR SUPERCONTINUUM LASER

ELECTRO MIR is based on LE VERRE FLUORE over 38 years' experience in fluoride fibers. **ELECTRO MIR** is built on a mature reliable technology, the laser is turnkey, easy to operate and delivered with real achromatic collimated output to ensure a perfect collimation over its wide spectral range.

— Supercontinuum lasers
— SCIENTIFIC
— NIR - MID IR



OPTICAL SPECIFICATIONS		ELECTRO MIR 4.1	ELECTRO MIR 4.8
Spectral bandwidth	mini	< 900 nm	< 900 nm
	max	> 4100 nm	> 4800 nm
Total average power		> 800 mW (typ. 1W)	> 500 mW (typ. 600 mW)
Repetition rate		250 kHz	
Seed pulse width		> 1 ns	
Power stability		< +/- 1 %	
Spatial mode		Singlemode	
Polarization state		Unpolarized	
Output connection		FC/APC Collimator (~1,5 meter armored cable)	
Synchronization output		External trigger output	
Interlock connector		2-pin LEMO	
OTHER SPECIFICATIONS			
Control interface		Front panel and GUI	
Operating temperature		+15°C to +35°C non condensing	
Weight		< 14 kg	
Dimensions (LxWxh)		320x320x145 mm	
Power requirements		100-240 V, 50/60 Hz	



ADDITIONAL EQUIPMENT

Achromatic collimated output

Easy fiber coupling with Pop

Tunable filters : Salsa, monochromators, custom

OPTION

External or internal trigger

LEUKOS
Make a bright future

+33 (0)5 87 20 00 25

contactus@leukos-laser.com

www.leukos-laser.com

All specifications are subject to change without notice - JANUARY 2023 EDITION



CAUTION – VISIBLE AND INVISIBLE
LASER RADIATION AVOID EYE AND
SKIN EXPOSURE TO DIRECT OR
SCATTERED RADIATION
CLASS 4 LASER PRODUCT